





YOKOGAWA CORIOLIS MASSFLOWMETER - ROTAMASS

Versatile and durable pensity measurements. Flow & Density measurements.





RotaMASS - Remote Version RotaMASS - Compact Version

Whenever the task is to measure massflow, density, temperature and volume flow, the RotaMASS is the right choice.

- M/E fuel consumption
- \Rightarrow A/E fuel consumption

- \Rightarrow Process control
- \Rightarrow Bunker meter

The RotaMASS 3 Series is the best-in-class mass flowmeter featuring discrete, parallel, thick-walled, seamless tubes that are uniquely decoupled from process vibration and pipeline stress.

This highly precise Coriolis measurement principle is not affected by anything: neither through the physical properties of the medium, nor through environmental conditions. Even fluctuating pressures and changes in viscosity or temperature do not change the accuracy of the measurement results.

Coriolis principle: Electromagnetic forces set up resonant vibrations of the measurement tubes. Coriolis forces acting on the medium flowing through the tubes alter these vibrations by small amounts. The interaction between the resonance vibrations of the tubes and the small deviations caused by the Coriolis forces results in a small phase shift, which is detected by two electromagnetic pickups. It is this small phase shift, which is measure the mass flow. At the same time the resonance frequency serves to measure the density of the medium.



Performance data:

 \Rightarrow

- Direct flow measurement (mass an \Rightarrow volume), Density and Temperature measurement
- Online calculation of Density15 and \Rightarrow Viscosity50
- AIR in oil detection \Rightarrow
- \Rightarrow Full data log of every parameter available in the system
- \Rightarrow Unique "box-in-box" design
- \Rightarrow Paired balanced metering tubes
- Excellent zero and long term stability

- High accuracy and high stability over a wide range
- \Rightarrow Available in explosion proof versions
- Simple installation \Rightarrow
- High temperature design \Rightarrow (-200°C up to 350°C)
- \Rightarrow Up to 295 bar
- No filter necessary \Rightarrow
- \Rightarrow No by-pass needed
- \Rightarrow Mounting solutions:

removabel, skids and fixed

Your reliable partner for marine measuring instruments and service



D-25368 Kiebitzreihe

Tel.: +49 (0) 4121 / 491 6890 E-Mail: office@txmarine.com

Fax: +49 (0) 4121 / 463 48 74 Internet: www.txmarine.com







YOKOGAWA CORIOLIS MASSFLOWMETER - ROTAMASS

Technical data

	. Common data
Available models:	Remote detector - RCCS34 to 39/XR: 2 tube design Integral detector - RCCT34 to 39/XR: 2 tube integral design
Nominal diameter:	DN15-DN200
Mass Flow Measurement:	DN13 DN200
measuring range:	Qmax t/h 5 up to 600*
	Qnom t/h 3 up to 500*
Accuracy mass flow:	± 0,1% of flow rate (+/- zero point stability)*1
Repeatability:	± 0,05%*1
Density Measurement:	
measuring range:	0,3kg/l to 2kg/l*
Accuracy:	0,02g/cm ³ - 0,0015g/cm ³
Repeatability:	± 0,0005g/cm ³
Temperature Measurement:	\pm 1°C / \pm 0,5% of reading
Process temperature:	-200°C - 150°C
Ambient temperature:	-50°C - 80°C
Communication Interface:	4-20mA, HART
Process connections:	Flanges DIN, ANSI, JIS (additional connections available)
Process pressure:	Up to 250bar
Display/Operation:	Free defineable up to 4-line backlight display
Power supply:	90-264V AC (47-63Hz); 20.5-28.8 V DC
I/O signal standard:	2 current outputs galvanic separted from other
	signals
	2 pulse / frequency (0-10 000 Hz),
	status outputs or passive transistor contact output,
	active or passive status input
	,

Mounting exampels:



Extract of reference list:

- OW Otilia
- OW Copenhagen
- OW baltic
- OW Scandinavia

Highlander

- OW Atlantic
- OW AtlanticVäderö
- •
- Thor Alpha Thor Omega OW Aalborg

Bayern

Wappen von

Your reliable partner for marine measuring instruments and service



TX Marine Messsysteme GmbH Sandkamp 18

Sandkamp 18
D-25368 Kiebitzreihe

Tel.: +49 (0) 4121 / 491 6890 E-Mail: office@txmarine.com Fax: +49 (0) 4121 / 463 48 74 Internet: www.txmarine.com

^{*} depends on model / *1 additional information technical information